

INTERCHANGE JOINTED BOROSILICATE GLASSWARE

Bends, recovery, vertical


Borosilicate Glass



Catalogue No.	Cone size to fit flask	Cone size to fit condenser
8SSBV/11	14/23	14/23
8SSBV/22	19/26	19/26
8SSBV/23	19/26	24/29
8SSBV/33	24/29	24/29
8SSBV/44	29/32	29/32

Bends with multiple connections (pig)

Borosilicate Glass




Catalogue No.	Socket size	Cone size
8SRVP/00	10/19	10/19
8SRVP/11	14/23	14/23
8SRVP/21	19/26	14/23
8SRVP/41	29/32	14/23

Thread type available.

If you wish to order thread type, please add SC to catalogue number. For e.g. 8SRVP/41SC

Bends with socket connection


Borosilicate Glass



Catalogue No.	Socket size	Cone size
8SRBS/11	14/23	14/23
8SRBS/22	19/26	19/26
8SRBS/23	19/26	24/29

Bends with vacuum connection

Borosilicate Glass




Catalogue No.	Socket size	Cone size
8SRAAV/11	14/23	14/23
8SRAAV/22	19/26	19/26
8SRAAV/23	19/26	24/29
8SRAAV/33	24/29	24/29
8SRAAV/44	29/32	29/32

Thread type available.

If you wish to order thread type, please add SC to catalogue number. For e.g. 8SRAAV/44SC

Bends with vent

Borosilicate Glass




Catalogue No.	Socket size	Cone size
8SRBV/00	10/19	10/19
8SRBV/11	14/23	14/23
8SRBV/22	19/26	19/26
8SRBV/23	19/26	24/29
8SRBV/33	24/29	24/29
8SRBV/44	29/32	29/32

Thread type available.

If you wish to order thread type, please add SC to catalogue number. For e.g. 8SRBV/44SC

Dreschel bottles

Borosilicate Glass



Catalogue No.	Capacity ml	Socket size
8SMF/29/3/125	125	24/29
8SMF/29/3/250	250	24/29
8SMF/29/3/500	500	24/29

See also Bottles on page 7 and 29

Drechsel bottle heads

Borosilicate Glass

Catalogue No.	Type	Cone to fit size	Porosity
8SDHP12/3	Plain	24/29 DB 12/3	—
8SDHP25/3	Plain	24/29 DB 25/3	—
8SDHP50/3	Plain	24/29 DB 50/3	—
8SDHS12/3	Sinter	24/29 DB 12/3	1,2 or 3
8SDHS25/3	Sinter	24/29 DB 25/3	1,2 or 3
8SDHS50/3	Sinter	24/29 DB 50/3	1,2 or 3

Please specify porosity of sinter and type when ordering

Columns, fractionating (Vigreux)

Borosilicate Glass



Catalogue No.	Socket/ cone size	Approx. effective length mm
8SCFV36/B24	24/29	360
8SCFV60/B24	24/29	600

Columns, chromatography with sintered disc porosity 0

Borosilicate Glass



Catalogue No.	Diameter	Effective length	Socket size
8SRI/10	10	100mm	14/23
8SRI/20	10	200mm	14/23
8SRI/30	10	300mm	14/23
8SRI/40	10	400mm	14/23
8SR2/10	20	100mm	19/26
8SR2/20	20	200mm	19/26
8SR2/30	20	300mm	19/26
8SR2/40	20	400mm	19/26
8SR2/50	20	500mm	19/26
8SR3/30	26	300mm	24/29
8SR3/40	26	400mm	24/29
8SR3/50	26	500mm	24/29
8SR5/40	30	400mm	34/35
8SR5/50	30	500mm	34/35
8SR6/40	30	400mm	40/38
8SR6/50	30	500mm	40/38

Condensers, air

Borosilicate Glass



Catalogue No.	Surface area cm ²	Socket size	Cone size	Effect length mm	Overall length mm
8SCA12/11	100	14/23	14/23	200	225
8SCA12/12	100	19/26	19/26	150	170
8SCA12/23	200	24/29	24/29	300	320
8SCA12/22	240	19/26	19/26	400	430
8SCA12/43	400	24/29	24/29	550	570
8SCA12/44	500	29/32	29/32	550	570

Cont'd page 20